

KSSGI4B20

[Print](#)


Additional Info

Rated Frequency (Hz):	2,730
Rated Voltage (Vo-p/VDC):	3.6
Current Consumption (mA):	Max.80
Sound Pressure Level (dB):	Min. 85dBA (Typical 90) @5cm
Coli Resistance(Ω):	20.0+/-3.0
Operating Voltage Range (Vo-p):	3.0~5.0
Operating Temperature (°C):	-30~+70
Storage Temperature (°C):	-40~+85
Dimension (mm):	8.5 x 8.5 x H3.0
Sound Demonstration:	click here

Tagged under [SMD External Circuitry Type Transducer](#)

More in this category: [« KSSGJ4B16-S](#) [KCVG084B16-A »](#)

[back to top](#)

