





Pos.	L _{-0.9}
-	-
3	7.62
4	10.16
5	12.7
6	15.24
7	17.78
8	20.32
9	22.86
10	25.4
11	27.94
12	30.48
13	33.02
14	35.56
15	38.1
16	40.64
17	43.18

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E1	NOTE 1 0.76μm PLATING UPDATE (PdNi+AuFLASH)	12JUL2023	BGC	PS



RECOMMENDED PCB-LAYOUT



1 MATING SIDE: Min 0.76μm (PdNi + Au FLASH) IN ZONE "F" OVER Min 1.27μm Ni

(Alternative plating – Min 0.76μm Au OVER Min 1.27μm Ni)




SOLDER SIDE: 3.0 – 5.0 μm TIN OVER MIN. 1.27μm NICKEL

2 PAY ATTENTION THE POSITION OF 1st CONTACT


KONTAKTSTIFT / CONTACT PIN	CuZn	1	2
STIFTGEHÄUSE / PIN HOUSING	PCT	SCHWARZ / BLACK	1
BENENNUNG EINZELTEIL PART DESCRIPTION	WERKSTOFF MATERIAL	OBERFLÄCHE / FARBE SURFACE / COLOR	SI No

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.HO 24MAR1995	 TE Connectivity Ltd.			
		CHK M.SCHAARSCHMIDT 24MAR1995				
		APVD —	NAME			
		PRODUCT SPEC 108-18012	AMPMODU II PINHEADER, SINGLE ROW, SMD-WITH PACKING TUBE.			
		APPLICATION SPEC —				
		WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-966306	RESTRICTED TO —
CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 2	REV E1		


P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—



POS. 1 OF PIN HEADER
IN PLACE 5 POS. SHOWN
POS. 1 DER STIFTLASTE
HIER 5 POL. GEZEICHNET



ODD NUMBER OF POSITION
UNGERADE POLZAHL



EVEN NUMBER OF POSITION
GERADE POLZAHL

POSITION IN TUBE
Lage in Verpackungsrohre

- 5 OBSOLETE
- 4 OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISI
- 3 SEE TABLE
SIEHE TABELLE
- 2 CENTERLINE OF PIN HEADER
MITTELLINIE DER STIFTLASTE
- 1 AMPMODU II SMD-PIN HEADER
SEE SHEET 1 OF 2.
AMPMODU II SMD-STIFTLASTE
SIEHE BLATT 1 VON 2.

1-966306-2	12	17
1-966306-0	10	20
966306-9	9	23
966306-8	8	25
4 966306-7	7	29
966306-6	6	34
5 966306-5	5	41
966306-4	4	51
966306-3	3	69
BESTELL-NR. PART NO.	POLZ. PROREIHE POLZ. PER ROW	VERPACKUNGS-EINHEIT PACKING UNIT

OBSOLETE



S.TABELLE SEE TABLE	4	3	ADAPTER	PCT-GV	SCHWARZ / BLACK	4
	3	3	AMPMODU II STIFTL., SMD	1	1	3
	2	2	VERSCHL. STIFT / LOCKS PIN	PP	ROT / RED	2
	1	1	VERPACKUNGSROHR / PACKING PIPE	ANTI-STATISCH	TRANSPARENT	1
ORDER-NR	POS.	STÜCK / PIECE	BENENNUNG EINZELTEIL PART DESCRIPTION	WERKSTOFF MATERIAL	OBERFLÄCHE / FARBE SURFACE / COLOR	SI No

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: TOL ± 0.2
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH
MATERIAL SEE TABLE	SEE TABLE

DWN A.HO	24MAR1995
CHK M.SCHAARSCHMIDT	24MAR1995
APVD —	—
PRODUCT SPEC 108-18012	—
APPLICATION SPEC —	—
WEIGHT —	—



TE Connectivity Ltd.

NAME AMPMODU II PINHEADER, SINGLE ROW, SMD-WITH PACKING TUBE.			
SIZE A3	CAGE CODE 00779	DRAWING NO C-966306	RESTRICTED TO —
CUSTOMER DRAWING		SCALE 2:1	SHEET 2 OF 2
		REV E1	