

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREEPORT, MINNESOTA

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BA-2 RQ1

ABM0500

(M) BA-2 RQ1
ISSUE 4

REPLACES

RELEASE NO.

18 JAN 06

RJ

CHECK

REVISIONS

A CO 9600

R.E.R.

2 MAR 59

B CO14866

J.D.

8 AUG 60

C CO-34311

J.A.L.

20 JAN 75

D CO45448

D.J.W.

23 FEB 79

E CO 77580

SAD

10 JUN 94

F CO-82133

CSL

26 JUL 96

G CO-92159

CSL

21 JAN 98

H CO93346

DLT

25 AUG 98

J CO-94212-C

DLT

20 SEP 99

K 0018387

TSG

18 JAN 06

CHECK

59

FORMTEK

R.E.R.

2 FEB

59

DRAWN


BA-2 RQ1
PAGE 1 OF 1

M

DRAWING
NUMBER

ISSUE

14



NOTES

- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- ② HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — — — 14-22 OZ
RELEASE FORCE — — — — — 10 OZ MIN
DIFFERENTIAL TRAVEL — — — .002-.0075
OVERTRAVEL — — — — — .219 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L23 20A 125, 250 OR 480 VAC
10A 125 VAC "L"
1HP 125 VAC, 2HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC

L288
L308
L315



20(3)A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:
ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT .080 LB