

HDMI over Cat5/6 Extender, Pigtail-Style Receiver for Video/Audio, USB Powered, Up to 125 ft., TAA

MODEL NUMBER: **B126-1A0-U**



Works with Tripp Lite's B126-Series transmitters to extend an HDMI audio/video signal via Cat5e/6 cable to an HDMI display up to 125 ft. Ideal for digital signs, schools, retail settings and trade show presentations.

Description

The B126-1A0-U HDMI over Cat5/Cat6 Active Extender works with Tripp Lite's B126-002 or B126-004 transmitter to extend an HDMI audio/video signal to an HDMI projector, monitor or television. It's ideal for digital signs, trade shows, presentations, classrooms, churches, retail settings and other applications where the video source is located farther than conventional cables allow. A latching HDMI connector on the built-in cable provides a more secure connection

The receiver's built-in HDMI cable connects to the display. Cat5e/6 cable connects the receiver to the B126-Series transmitter (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series). Power is supplied by the included USB Micro-B to USB-A cable, which connects between the receiver and a USB port on the display or a USB wall charger.

The B126-1A0-U can extend a 1080p (@ 60 Hz) signal up to 125 feet with full, rich stereo. Built-in RJ45 LEDs indicate the units are receiving power and a signal from the source. Built-in equalization control lets you fine-tune the image quality at the display. Easy to set up with no software or drivers to install. Works with all operating systems and HDMI sources.

Features

Extends HDMI Audio/Video Signals to an HDMI Display

- Extends a 1080p (@ 60 Hz) signal up to 125 ft.
- Ideal for digital signs, trade shows, presentations, classrooms, churches and retail settings
- Built-in cable includes latching HDMI connector for a more secure connection

Highlights

- Supports high-definition video resolutions up to 1080p (@ 60 Hz)
- Supports stereo audio and HDCP
- Works with all operating systems and HDMI sources
- Built-in cable includes latching HDMI connector for a more secure connection
- Plug and play—no software, drivers or external power supply
- Built-in equalization control lets you adjust monitor image

System Requirements

- Display with HDMI port

Package Includes

- B126-1A0-U Receiver unit
- USB Micro-B to USB-A cable, 3 ft.
- Screwdriver for adjusting equalization
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Connects to transmitter with one Cat5e/6 cable (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series)
- Supports stereo audio and HDCP
- Built-in equalization control lets you adjust the image

Easy to Set Up and Use

- Plug-and-play engineering—no software, drivers or external power supply
- Powered via included USB cable
- Connects quickly to display with built-in HDMI cable
- LEDs indicate when units are receiving power and a signal from the source
- Works with all operating systems and HDMI sources

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332190253
Technology	HDMI
INPUT	
Bus Powered	Yes
Product Length (in.)	8.4
POWER	
LED Indicators	Green (Power), Orange (Activity)
PHYSICAL	
Color	Black
Material of Construction	Polycarbonate
Rackmountable	No
Shipping Dimensions (hwd / cm)	3.30 x 15.60 x 12.19
Shipping Dimensions (hwd / in.)	1.30 x 6.14 x 4.80
Shipping Weight (kg)	0.11
Shipping Weight (lbs.)	0.25
Unit Dimensions (hwd / cm)	2.4 x 6.1 x 5.2
Unit Dimensions (hwd / in.)	0.9 x 2.4 x 2



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.09
ENVIRONMENTAL	
Operating Temperature Range	14 to 167 F (-10 to 75 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Relative Humidity	0% to 85%, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	125
Signal Range (m)	38
CONNECTIONS	
Ports	1
Side A - Connector 1	MICRO-USB B (FEMALE); RJ45 (FEMALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	1080p @60Hz
HDMI Specification	1.4
HDCP Specification	1.4
Audio Specification	Stereo
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
Max Supported Color Depth	24-bit True Color
3D Video Supported	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>