



Part Number : [1301090009](#)
Product Description : Safeway Nylon 100W Hand Lamp with Molded, 16/3 SJTOW Cord Type, Metal Guard, Overall Cord Length 15.24m (50.0')
Series Number : 130109
Status : Active
Product Category : Lamps and Lights
Engineering Number : 405



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130109
Description	Safeway Nylon 100W Hand Lamp with Molded, 16/3 SJTOW Cord Type, Metal Guard, Overall Cord Length 15.24m (50.0')
NEMA Configuration	NEMA 5-15
Product Name	Safeway
Type	Hand Lamps
UPC	78678861603

Agency

UL	E59049
----	--------

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Incandescent
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SJTOW
Depth	N/A
Duty	Commercial
Guard Included	Yes
Guard Type	Steel
Height	N/A
Lamp Type	A21

Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Net Weight	1876.056/g
Outlet	None
Packaging Type	Carton

This document was generated on Sep 22, 2025