







1. MANUFACTURE TO BE COMPLIANT WITH EU RoHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN 1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
2. **ELECTRICAL SPECIFICATIONS** ARE SHOWN FOR REFERENCE ONLY. FOR OPERATING, PAIRING AND USAGE INSTRUCTIONS PLEASE SEE TE DATA SHEET AT LATEST REVISION
1. FREQUENCY: SEE TABLE
2. ELECTRONIC ASSEMBLY IAW IPC-A-610
3. FREQUENCY DESIGNATION REPRESENTED BY "FFF".
4. PROGRAMMING FUNCTION INDICATED BY "PP"
3. **ENVIRONMENT:**
1. USAGE TEMPERATURE: -40 TO 85°C
2. KEY SWITCH IS INTENDED FOR A SINGLE FUNCTION REMOTE SEE RELATED PARTS LIST FOR MULTI-FUNCTION VARIATIONS
4. **USAGE APPLICATION NOTES:**
1. REPLACE BATTERY WITH CR2032 COIN CELL WHEN APPLICABLE. SEE DATA SHEET FOR METHOD
2. AVOID LEAVING UNIT IN PLACES OF HIGH SOLAR LOADING TO PREVENT DAMAGE.
3. AVOID PLACES OF HIGH CHEMICAL CONTENT SUCH AS CHLORINE OR FUEL/HYDRAULIC VAPOR.
4. UNIT SHOULD NOT EXPERIENCE SIGNIFICANT SHOCK FROM DROPPING TO HARD SURFACES. TOP LOOP IS INTENDED FOR A LANYARD NOT A STEEL KEY RING.
5. THIS CAN BE A "MADE TO ORDER" OEM PRODUCT. SEE YOUR SALES REPRESENTATIVE FOR DETAILS.
- PACKAGING NOTES:**
6. WRAP UNITS IN BUBBLE SLEEVE TO PROTECT FINISH.
7. PACK FLAT 10/ LOT BAG
8. PLACE IN CONTAINER OF 150 UNITS

TABULATION MATRIX		
TCPN	DESCRIPTION	PRODUCT REVISION
OTX-418-HH-KF1-DS	REMOTE DS 418MHZ OOK AM 1BTN KF TX FCC	B
OTX-418-HH-KF1-HT	REMOTE HT 418MHZ OOK AM 1BTN KF TX FCC	B
OTX-418-HH-KF1-MS	REMOTE MS 418MHZ OOK AM 1BTN KF TX FCC	B
OTX-433-HH-KF1-DS	REMOTE DS 433MHZ OOK AM 1BTN KF TX FCC	B
OTX-433-HH-KF1-HT	REMOTE HT 433MHZ OOK AM 1BTN KF TX FCC	B
OTX-433-HH-KF1-MS	REMOTE MS 433MHZ OOK AM 1BTN KF TX FCC	B

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JHAGER 10/13/23		TE Connectivity				
		CHK CLEWIS 10/13/23						
DIMENSIONS: mm [INCH]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 2.0 1 PLC ± 1.0 2 PLC ± .50 3 PLC ± 4 PLC ± ANGLES ± 30'		NAME				
				REMOTE HANDHELD FFFMHz OOK AM 1BTN KF TX FCC				
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
PC DK-P				A3	00779	OTX-FFF-HH-KF1-PP	—	
CUSTOMER DRAWING						SCALE	SHEET	REV
						2:1	1 OF 2	A



LIST OF ITEMS AND MATERIALS	
ITEM	DESCRIPTION
1	OTX TRANSMITTER ASSEMBLY
2	KF1 SINGLE ACTIVATION KEY-PAD
3	KF1 SINGLE ACTIVATION KEY-PAD INSERT
4	KEY-FOB TRANSMITTER HOUSING TOP
5	KEY-FOB TRANSMITTER HOUSING BTM
6	KEY-FOB FCC IDENTIFICATION LABEL
7	BATCOIN001

THIS DRAWING IS A CONTROLLED DOCUMENT.				 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC 1 PLC SEE SHEET 1 FOR TOLERANCE LIST 2 PLC 3 PLC ± 4 PLC ± ANGLES ± 30'		NAME REMOTE HANDHELD FFFMHz 00K AM 1BTN KF TX FCC	
		PRODUCT SPEC —		SIZE A3	
		APPLICATION SPEC —		CAGE CODE 00779	
MATERIAL		WEIGHT 0.03 g		DRAWING NO C-0TX-FFF-HH-KF1-PP	
		CUSTOMER DRAWING		RESTRICTED TO —	
				SCALE 2:1	
				SHEET 2 OF 2	
				REV A	