

STANDARD CIRCULAR CONNECTORS



✓ Active

TE CONNECTIVITY (TE)

983-0SE 12-12 PN-A1208

DEUTSCH | 983

983-0SE 12-12 PN-A1208

TE Internal Number: ZPF000000000109804

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

Product Type Connector

Sealable Yes

Shell Material Stainless Steel

Operating Temperature Range -65 – 260 °C [-85 – 500 °F]

Shell Size 12

DOCUMENTATION

Catalog Pages/Data Sheets

DEUTSCH 983 Series

PDF

[English](#)

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Product Type Connector

Sealable Yes

Shell Size 12

Shielded Yes

Connector Style Receptacle

Shell Type Square Flange Receptacle

Body Features

Shell Material Stainless Steel

Contact Features

Contact Layout 12 – 12

Contact Type Male Contact

Mechanical Attachment

Mating Alignment Type Keyed

Usage Conditions

Operating Temperature Range -65 – 260 °C [-85 – 500 °F]

Statement of Compliance

Statement of Compliance

PDF
