

208M914-19B10 Product Details

[Share](#) [Print](#) [Email](#)


✓ Active

Braid, Fixed, Spin and Tinel Lock Adapters

208M914-19B10

208M914-19B10

TE Internal Number: 128431-000

Product Highlights [View All](#)

- Applies To Cable
- Military Style Number = MIL-DTL-38999
- Style = Braided
- Connector Code = 40
- 90°

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Style ?	Braided
Angle ?	90°
Connector Shell Size	14
Finish	Cadmium Plating over Electroless Nickel
Color	Olive Drab

Dimensions

Boot Diameter (mm [in]) ?	21.10 [0.831] ▼
---------------------------	-----------------

Body Features

Connector Code ?	40
Entry Size	10
Material	Aluminum Alloy

Configuration Features

Braid ?	Preattached Single 36 AWG Braid
Industry Standards	
Government/Industry Qualification	No
Military Style Number	MIL-DTL-38999
RoHS/ELV Compliance ?	Not ELV/RoHS compliant
Lead Free Solder Processes ?	Not relevant for lead free process ▼

Conditions for Usage

Applies To	Cable
------------	-------

Other

Brand	Raychem
Comment	For Specific shell size information, refer to Harnware™ or Catalogue.

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

