

T 3327 000 U

Description	Female panel connector 4 pole IP40; solder; silver; bayonet locking
IP-class mated	IP40
number of positions (w/o PE)	4
rated current (40 °C)	5 (A)
rated voltage	300 (V)

active

Please log in to receive your price.

2,28 €
price

Total price
228,00 €
Your net plus VAT

100 pcs.

The minimum order amount is 100 pcs.; packing unit 100 pcs.
500 pcs. ready for shipping.

add to cart

add to favorite

send request

Technical data | Downloads

General Characteristics		
contact diameter		1,5 mm
gender		female
IP-class mated		IP40
locking system		bayonet ring
number of positions (w/o PE)		4
part category		female receptacle
termination		solder pin
Further Characteristics		
max. wire gauge		0.5
min. wire gauge		0.05
RoHS Compliant Yes		X
Electrical Characteristics		
rated current (40 °C)	(A)	5
rated voltage	(V)	300

Downloaded from Arrow.com.