All orders placed will be shipped out as usual, delivery times are expected to be affected due to COVID-19.Thank you for your continued support. Read More

Register to Get $10 Shipping Coupon



240W DC-DC Converter 24V@10A

SKU:FIT0172 Brand:DFRobot Reward Points: 450

* Model: 7.5V@5A | 9V@5A | 12V@6A | 12V@10A | 24V@6A | 24V@10A

Quantity: - +

ADD TO CART

Frequently Bought Together

240W DC-DC Converter 24V@10A + 72W DC-D... 12V@6A + 38W DC-D... 7.5V@5A + 45W DC-DC ... 9V@5A + 120W DC-DC =

You have choosen:0
Total amount:

BUY IT NOW

INTRODUCTION

This is a waterproof DC-DC converter. With 8-18V DC input, it converts to 24V@10A which is an ideal supply for robots.

Note: Input voltage of 12V or above can reach 240W. Transmission line with line diameter of 2.5 square mm or above should not be too long.
The power input can be supplied by battery for better effect.

FEATURES

- Overvoltage protection
- Overcurrent protection
- Overheat protection
- Short-circuit protection
- Waterproof and shockproof case
- High efficiency and less heat

SPECIFICATION

- Input Rage: 8-18V DC
- Output: 24V DC
- Output Current: 10A(max)
- Size: 74 X 74 X 32mm(2.91x2.91x1.26")
- Efficiency: 82%-88%
- Weight:0.28Kg
- Maximum working temperature:80 ℃


Downloaded from Arrow.com.

SHIPPING LIST

- 240W DC-DC Converter(FIT0172) x1

REVIEW

FAQ



Sign up for exclusive offers!

Your email address →

Like us on

Downloaded from Arrow.com.