



Products

Customize Your Parts

Industries Solutions

Search

News & Events

First Time?



(0)



Home / Products / M Series / M12 (A)

## Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

M Series >

Accessory

M5

Guided M8

M8

M10.5

M12 (A)

M12 (B)

M12 (D)

M12 (I)

M12 (K)

M12 (L)

M12 (S)

M12 (T)

M12 (X)

M23

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



### M12A-05PMMC-SF8C50

Operating Temperature: -20°C ~ +85°C

Transmission Speed: N/A

Shielded: Metal, Non-shielded

Jacket Material: PVC

Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity - 1 +

Add to Cart

Inquiry



Can't find? [Customize your part](#)

### Mating Pair & Accessories

Connector Type

Search

M Series, CAP-WBDMQPC1  
-20°C ~ +80°C

M Series, CAP-WBDMSMA2  
-40°C ~ +105°C

M Series, CAP-WBDMSPB2  
-40°C ~ +105°C

M Series, IA-A05F-A05F  
-20°C ~ +85°C

M Series, LM12A-05BFFM  
-20°C ~ +80°C

M Series, LM12A-05BFFM  
-20°C ~ +80°C

- 0 +

- 0 +

- 0 +

- 0 +

- 0 +

- 0 +

Specifications	Download / CAD
Nominal Current <b>4A</b>	Connector Type <b>Receptacle With Wires</b>
Shielded <b>Metal, Non-shielded</b>	No. of Contacts <b>05</b>
Connector Gender <b>Male</b>	Backshell <b>Hexagonal</b>
Mating Style <b>Screw Thread</b>	IP Rating <b>IP68</b>
Assembly Style <b>Crimp</b>	
<a href="#">More Options</a>	

### People Also Bought

