Part Number : 936000348
Product Description : Heavy-Duty Plastic Gable Gland with Gasket and Nut, M16x1.5 Thread, Light Grey RAL 7035
Series Number : 93600
Status : Active
Product Category : Heavy-Duty Cable Glands
Engineering Part Number : 7000.7822.7



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Plastic Gable Gland with Gasket and Nut, M16x1.5 Thread, Light Grey RAL 7035
Cable Gland Type	IP68 with Nut and Gasket
IP Rating	IP68
Product Name	Heavy-Duty Connectors
Standard	DIN EN 50262, EN 60529
UPC	887191851600

Physical

Cable Diameter	4.00-8.00mm
Gland Color	Light Grey RAL 7035
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Nut	Polyamide
Net Weight	7.500/g
Packaging Type	Bag
Panel Cutout Diameter	16.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +100°C
Thread Size	M16x1.5
Thread Type	(M) Metric
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

Mates With / Use With

Downloaded from Arrow.com.

Use with Part(s)

Description	Part Number
Use With	Sealed enclosures and boxes

Downloaded from Arrow.com.