



Products

Customize Your Parts

Industries Solutions

Search

News & Events

First Time?



(0)



Home / Products / M Series / M12 (A)

Product Line

DeepTronica >

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

M Series >

Accessory

M5

Guided M8

M8

M10.5

M12 (A)

M12 (B)

M12 (D)

M12 (I)

M12 (K)

M12 (L)

M12 (S)

M12 (T)

M12 (X)

M23

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



M12A-08PFFS-SF8B15

Operating Temperature: -20°C ~ +85°C

Transmission Speed: N/A


Shielded: Metal, Non-shielded

Jacket Material: PVC

Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity - 1 +

 Add to Cart

 Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

 Search

- 0 +


- 0 +

- 0 +

- 0 +

- 0 +

- 0 +

 Add to Cart

 Inquiry

Specifications

Download / CAD

Nominal Current

2A

Connector Type

Receptacle With Wires

Shielded

Metal, Non-shielded

No. of Contacts

08

Connector Gender

Female

Backshell

Hexagonal

Mating Style

Screw Thread

IP Rating

IP68

Assembly Style

Solder

 More Options

People Also Bought



M12A-08PFFS-...



M12A06FR-12AFR-...



FLBB-05FGMS-GCP-...



M12A-08BFFM-...



APTM-BMZFA012-001