Datasheet for part number ECIER3223-015S0K1A0B1

Our Catalog Part Number: ECIER3223-015S0K1A0B1
Our Global Manufacturing Part Number: 132056-7024
Brand: Cannon Product Category: EV Product Line: EV Series: EV

Product Datasheet	
Series	EVC IEC 62196 Type 2 Connector EVSE Rear mount outlet
Product Image	Current Rating
32A	Cable Rating
Level 2	Powering System
Three phase (480VAC)	Cable Length
1,5 m	Compression Limiter/Metal Inserts in Flange Holes
Without compression limiter/ inserts	Dust Cap/ Spring Cap
With mounting ring thin (metal insert M4)	Drain Spout
With Drain spout, without tube	Locking Device
No locking device	Rubber Boot
No rubber boot supplied	Mounting Hole Pattern
58x61mm	Flange Gasket
With flange gasket	Temperature Range
-30°C to +50°C	Durability
10,000 mating cycles min	Sealing Requirements
IP 44 min per IEC 61851-1 and tested in accordance with IEC 60525	Certifications Connector
CE, ETL, IEC 62196-1 and IEC 62196-2	Certifications Cable
DIN EN 50620	Product Drawing

Specifications and dimensions subject to change.

Downloaded from Arrow.com.