

Pushbutton, 16.2 mm, momentary contact function, 1 NO, bezel red



Description

Pushbutton with mounting hole diameter 16.2 mm, screw terminal, non-illuminated

technical data

> general

Bezel color	red
Property of bezel / mushroom	opaque
Collar shape	round
Operating temperature, min.	-25 °C
Operating temperature, max.	85 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	90 °C
illuminated	No
Packaging	Box
Packaging unit	100 pcs.
Net weight	11 g
Operating life	150,000 cycles
B10	195,000 cycles
Degree of protection, front side,	IP40
according to DIN EN 60529	IP65
	IP65 with sealing cap
Minimum order quantity (MOQ)	100 pcs.
RoHS compliant	Yes
REACH compliant	Yes
Country of origin	HU

> mounting diameters

Outside dimension, length	20 mm
Outside dimension, width	20 mm
Outside dimension, height	50 mm
Mounting hole	16.2 mm
Mounting depth	41 mm
Installation height	9 mm

> mechanical data

Terminal on the rear	Screw terminal
Fixing	Threaded ring
Actuation function	momentary contact function
Operating force, min.	7,5 N

direct links

> RAFI eCatalog

Operating travel, max.	4.3 mm
Contact function	1 NO
Contact system	Bridge contact
Contact material	Silver

> **electrical data**

Rated voltage, max.	250 V
Rated current, max.	2 A

drawings

Dimensioned drawing

