

MUSB, MUSBR, UUSB SERIES

MINI & MICRO USB 2.0 INTERFACES

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?MUSB, www.samtec.com?MUSBR-A or www.samtec.com?MUSBR-B

Insulator Material:

High Temperature Thermoplastic

Contact Material:

Phosphor Bronze

Shell Material:

Brass

Plating:

Gold on Mating Area, Nickel on Shell, Tin on Tails

Operating Temp Range:

-50°C to +85°C

Voltage Rating:

30 VRMS

Contact Resistance:

50 mΩ

Minimum Cycles:

1500

Packaging:

Packaged and shipped in Bulk Packaging Trays; Trays suitable for automation are available upon request.

RoHS Compliant:

Yes

Lead-Free Solderable:

Yes

TYPE

MUSB
= Mini USB 2.0

MUSBR
= High Retention Mini USB 2.0

NO. OF CONTACTS

-05

PLATING

-F
= Gold Flash on Mating Area, Tin on Tails

-S
= 30μ" (0.76 μm) Gold on Mating Area, Tin on Tails

COLOR

Leave blank for MUSB
-O
= Orange

TYPE


-B
= B Type (MUSB & MUSBR)

-AB
= AB Type (MUSB only)


-A
= A Type (MUSBR only)

OTHER SOLUTIONS


- Mini USB-A Type. Contact Samtec.




-A TYPE



-AB TYPE



-B TYPE



SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?UUSB-AB or www.samtec.com?UUSB-B

Insulator Material:

Black LCP

Contact Material:

Copper Alloy

Plating:

Au over 50μ" (1.27 μm) Ni

Shield Plating:

Sn over 50μ" (1.27 μm) Ni

Operating Temp Range:

-30°C to +80°C

Voltage Rating:

100 VAC

Contact Resistance:

50 mΩ

Cycles:

10,000

RoHS Compliant:

Yes

TID Numbers:

UUSB-AB-S-S-SM-TR

(61001772)

UUSB-B-S-S/F-SM

(61001571)

UUSB

UUSB
= Micro USB 2.0

TYPE

-AB
= Micro AB

-B
= Micro B

PLATING

-F
= Gold Flash on Mating Area and Tails


-S
= 30μ" (0.76 μm) Gold on Mating Area, Gold Flash on Tails

TERMINATION


-SM
= Surface Mount

TR


-TR
= Tape & Reel



-AB TYPE



-B TYPE



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329

SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0

SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292

SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385

CHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685