


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	29MAY2015	DW	CW
	A1	ECR-17-008664	17JUN2017	CH	CW
	B	ECR-20-014876	06NOV2020	WQR	CW









SCALE 3:5

TYPE 2: LOW CONSTRUCTION, TOP ENTRY
WITH STEEL DOUBLE LOCKING
OTHER SPEC REFER TO TYPE 1
类型2： 低结构，顶出，带彩锌双扣，其它规格参照类型1

NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: POWDER COATED, GREY
DEGREE OF PROTECTION: IP65 (MATED)

注释：
1. 技术参数：
上壳材料： 铝合金
表面处理： 灰色粉末喷涂
防护等级： IP65(配合)





SCALE 3:5

TYPE 1: LOW CONSTRUCTION, SIDE ENTRY
WITH STEEL DOUBLE LOCKING
类型1： 低结构，侧出，带彩锌双扣

PART NUMBER 料号	PART DESCRIPTION 描述	PG/M THREAD 1 PG/M 螺纹孔1	PG/M THREAD 2 PG/M 螺纹孔2	TYPE 类型
T1260242132-000	H24B-TGB-M32	H24B HOOD, TOP ENTRY M32, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳，顶出M32，彩锌双扣，灰色粉末喷涂	-	M32	TYPE 2 类型2
T1260242129-000	H24B-TGB-PG29	H24B HOOD, TOP ENTRY PG29, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳，顶出PG29，彩锌双扣，灰色粉末喷涂	-	PG29	
T1260242125-000	H24B-TGB-M25	H24B HOOD, TOP ENTRY M25, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳，顶出M25，彩锌双扣，灰色粉末喷涂	-	M25	
T1260242121-000	H24B-TGB-PG21	H24B HOOD, TOP ENTRY PG21, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳，顶出PG21，彩锌双扣，灰色粉末喷涂	-	PG21	
T1260240000-000	H24B-TGB	H24B HOOD, NO ENTRY, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳，无开孔，彩锌双扣，灰色粉末喷涂	-	-	
T1250242132-000	H24B-TSB-M32	H24B HOOD, SIDE ENTRY M32, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳，侧出M32，彩锌双扣，灰色粉末喷涂	M32	-	TYPE 1 类型1
T1250242125-000	H24B-TSB-M25	H24B HOOD, SIDE ENTRY M25, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳，侧出M25，彩锌双扣，灰色粉末喷涂	M25	-	
T1250242121-000	H24B-TSB-PG21	H24B HOOD, SIDE ENTRY PG21, METAL DOUBLE LOCKING, POWDER COATED, GREY H24B上壳，侧出PG21，彩锌双扣，灰色粉末喷涂	PG21	-	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL -
FINISH -

DWN DAVID.WANG 29MAY2015
CHK CHRIS.WANG 29MAY2015
APVD XIANG.XU 29MAY2015
PRODUCT SPEC 108-137013
APPLICATION SPEC 114-137013
WEIGHT -

TE Connectivity

NAME H24B-TSB/TGB/TSBH/TGBH-M/PG


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-T12X024XXXX000	-


Customer Drawing | SCALE 1:1 | SHEET 1 OF 2 | REV B


Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-








SCALE 3:5


NOTES:

SEE SHEET 1

TYPE 4: HIGH CONSTRUCTION, TOP ENTRY
WITH STEEL DOUBLE LOCKING
OTHER SPEC REFER TO TYPE 3
类型4： 高结构，顶出，带彩锌双扣，其它规格参照类型3

PART NUMBER 料号	PART DESCRIPTION 描述	PG/M THREAD 1 PG/M 螺纹孔1	PG/M THREAD 2 PG/M 螺纹孔2	TYPE 类型
TI280242140-000	H10B-TGBH-M40	H24B HOOD, TOP ENTRY M40, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳，顶出M40，彩锌双扣，高结构，灰色粉末喷涂	-	M40	TYPE 4 类型4
TI280242132-000	H24B-TGBH-M32	H24B HOOD, TOP ENTRY M32, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳，顶出M32，彩锌双扣，高结构，灰色粉末喷涂	-	M32	
TI280242129-000	H24B-TGBH-PG29	H24B HOOD, TOP ENTRY PG29, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳，顶出PG29，彩锌双扣，高结构，灰色粉末喷涂	-	PG29	
TI280242125-000	H24B-TGBH-M25	H24B HOOD, TOP ENTRY M25, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳，顶出M25，彩锌双扣，高结构，灰色粉末喷涂	-	M25	
TI280242121-000	H24B-TGBH-PG21	H24B HOOD, TOP ENTRY PG21, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳，顶出PG21，彩锌双扣，高结构，灰色粉末喷涂	-	PG21	
TI270242140-000	H24B-TSBH-M40	H24B HOOD, SIDE ENTRY M40, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED,GREY H24B上壳，侧出M40，彩锌双扣，高结构，灰色粉末喷涂	M40	-	TYPE 3 类型3
TI270242132-000	H24B-TSBH-M32	H24B HOOD, SIDE ENTRY M32, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED,GREY H24B上壳，侧出M32，彩锌双扣，高结构，灰色粉末喷涂	M32	-	
TI270242129-000	H24B-TSBH-PG29	H24B HOOD, SIDE ENTRY PG29, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED,GREY H24B上壳，侧出PG29，彩锌双扣，高结构，灰色粉末喷涂	PG29	-	
TI270242121-000	H24B-TSBH-PG21	H24B HOOD, SIDE ENTRY PG21, METAL DOUBLE LOCKING, HIGH CONSTRUCTION, POWDER COATED,GREY H24B上壳，侧出PG21，彩锌双扣，高结构，灰色粉末喷涂	PG21	-	





SCALE 3:5

TYPE 3: HIGH CONSTRUCTION, SIDE ENTRY
WITH STEEL DOUBLE LOCKING
类型3： 高结构，侧出，带彩锌双扣

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL -
-

FINISH -
-

DWN 29MAY2015 DAVID.WANG
CHK 29MAY2015 CHRIS.WANG
APVD 29MAY2015 XIANG.XU
PRODUCT SPEC 108-137013
APPLICATION SPEC 114-137013
WEIGHT -

TE Connectivity

NAME H24B-TSB/TGB/TSBH/TGBH-M/PG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-TI2X024XXXX000	-

Customer Drawing | SCALE 1:1 | SHEET 2 OF 2 | REV B

Downloaded from Arrow.com.