

Home: >

Part Number: 52807-0430

Image not available

Status: Active - Custom
Series: [52807](#)
Category: Molex Parts

[CHECK DISTRIBUTOR INVENTORY](#)

[Add to My Parts](#)

Series image - Reference only

Product Environmental Compliance

EU ELV:Not Relevant

EU RoHS:Compliant

EU RoHS Phthalates:Not Contained

China RoHS: 

REACH SVHC:Not Contained Per -
ED/01/2018 (15 January 2018)

Low-Halogen Status:Not Low-Halogen



Product Compliance Statement



EU RoHS Certificate of Compliance (PDF)



Multiple Part Product Compliance
Statements
EU RoHS, REACH SVHC, & Low-Halogen



Multiple Part Industry Compliance
Documents

*IPC 1752A Class C
*IPC 1752A Class D
*Molex Product Compliance Declaration

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Questions on Product Environmental Compliance? Email Product.Compliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

PRODUCTS+

Product Categories
Product Index
Industries


QUICK LINKS+

Company Information
Contact Molex
Cross-Reference
Koch Industries
Investor Relations
Literature
Press Room / Press Releases
Sitemap
Terms & Conditions

RESOURCES+

Supply Chain Transparency
Business Continuity
Compliance
ecocare
Help
Jobs
Legal | Trademarks
Supplier Portal
Privacy Policy
Tradeshows

STAY CONNECTED



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2018