



Part Number : [1300150112](#)

Product Description : Mini-Change C-Size Receptacle with Leads 1/2" - 14 NPT Threads, Male (Straight) 19 Poles, 2.0m (6.56') Length

Series Number : 130015

Status : Active

Product Category : Circular Industrial Connectors

Engineering Part Number : 3R3N36E80M020




Documents and Resources

Drawings

[1300150112 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130015
Description	Mini-Change C-Size Receptacle with Leads 1/2" - 14 NPT Threads, Male (Straight) 19 Poles, 2.0m (6.56') Length
Comments	C-Size (1-1/8" - 16 UN-2A)
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended (pigtail)
UPC	78678846667

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	300V AC/DC

Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	2.0m
Material - Component	Gray Anodized Aluminum
Mounting Thread Size	PG16
Net Weight	286.400/g
Orientation	Straight
Panel Mount	Front
Poles	19
Temperature Range - Operating	-20° to +80°C

Wire/Cable Type	UL 1569
Wire Size (AWG)	18, 22

This document was generated on May 27, 2026