

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0733870021

Status:

Active

Overview:

Precision Compression-Mount Microwave Test Connectors

Description:

50 Ohms, Precision Test Connector, 2.4mm Jack Receptacle, 2 Hole Flange Mount, with 2 Screws 6.35mm, PCB Thickness 1.96-3.99mm

Documents:

Drawing (PDF)

Product Specification PS-89675-0410-001 (PDF)

Application Specification AS-89675-446-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	RF/Coax Connectors
Series	73387
Overview	Precision Compression-Mount Microwave Test Connectors
Product Name	2.40mm
Style	PCB
Type	Subminiature
UPC	884982517653
Wire/Cable Type	N/A
Physical	
Gender	Jack
Keying to Mating Part	None
Net Weight	2.115/g
Orientation	Straight
PCB Mounting	Surface Mount
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	Compression
Reverse Polar	No
Electrical	
Frequency	50 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-89675-446-001
Product Specification	PS-89675-0410-001
Sales Drawing	SD-73387-002-001, SD-73387-002-PKG



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

73387 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION