



[My Cart](#) | [My Part Lists](#) | [Sign In/Register](#)

[English \(Change\)](#)

Have a Question?
Chat with a Product
Information Specialist



What can we help you find?



[Products](#)

[Industries](#)

[Resources](#)

[About TE](#)

[My Account](#)

[Innovation](#)

[Support Center](#)

[Home](#) > [Products](#) > [Automotive](#) > [Product Feature Selector](#) > [Product Details](#)

1452421-1 Product Details

[Share](#)

[Print](#)

[Email](#)



1452421-1

TE Internal Number: 1452421-1

Active

[View 3D PDF](#)

Multiple Contact Point (MCP) & MCON Contact Systems

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- MCON Product Line, Multiple Contact Point (MCP) Product Line
- Accessory
- Accessory Type = Cover
- 90° Cable Exit Angle
- 58 Positions

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [154 pos. PCM connector \(96 and 58 pos.\) \(PDF, English\)](#)

Application Specifications:

- [154POS. CONNECTOR \(96POS. AND 58POS. CONNECTOR \) \(PDF, English\)](#)

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version E1\)](#)
- [3D Model \(IGES, Version E1\)](#)
- [3D Model \(STEP, Version E1\)](#)

[List all Documents](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Line = MCON, Multiple Contact Point (MCP)
- Product Type = Accessory
- Accessory Type = Cover
- Accessory Color = Black

Body Features:

- Cable Exit Angle = 90°
- Assembly Integration Feature = With
- Assembly Integration Type = Lever
- Used With = Socket Housing

Housing Features:

- Housing Material = PBT/ASA - GF20

Configuration Features:

- Number of Positions = 58

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Features:

- Packaging Method = Box
- Packaging Quantity = 300

Other:

- Brand = AMP

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

