molex



**Part Number :** 1301120166
**Product Description :** Construction Guard 1-1/2" Neck, 10" x 5"
**Series Number :** 130112
**Status :** Obsolete
**Product Category :** Portable Lighting Accessories
**Engineering Part Number :** 378V

## Documents and Resources

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Product not active |
| China RoHS | Product not active |
| EU ELV | Product not active |
| Low-Halogen Status | Product not active |
| REACH SVHC | Product not active |
| EU RoHS | Product not active |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

# Part Details

## General

| | |
|---|---|
| Status | Obsolete |
| Category | Portable Lighting Accessories |
| Series | 130112 |
| Description | Construction Guard 1-1/2" Neck, 10" x 5" |
| NEMA Configuration | N/A |
| Product Name | Woodhead |
| Type | Accessory |
| UPC | 78678862378 |

## Electrical

| | |
|---|---|
| Lamp Wattage - Maximum | N/A |
| Lumens | N/A |
| On/Off Switch | N/A |
| Voltage (Fixture) - Maximum | N/A |

## Physical

| | |
|---|---|
| Bulb Type | N/A |
| Cord Length - Primary | N/A |
| Cord Length - Secondary | N/A |
| Depth | 120.65mm (4.750") |
| Duty | Industrial |
| Guard Included | Yes |
| Guard Type | Insulated, Steel |
| Height | 241.30mm (9.500") |
| Lamp Type | PL13/41 |
| Length | N/A |
| Material - Guard | #8 Gauge Vinyl Coated Steel |
| Outlet | None |
| Packaging Type | Carton |

Obsolete



Downloaded from Arrow.com.