

By Burndy
Catalog # [YSM4C](#)

Uninsulated Parallel Splice For 26,813 - 42,613 cmils



Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

Specifications

Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size	12 AWG-10 AWG
Range	
Conductor - Copper Str Size	12 AWG-10 AWG
Range	
Conductor Type	CU C Solid-Size;CU C Str-Size

Dimensions

Dimension - Outside Diameter inch	0.38 in
Dimension - Strip Length inch	9/16

General

Sub Brand	HYLINK
Die Index	8
Color Code	Gray
Trade Name	HYLINK™
Feature - Barrel Style	Chamfered
Type	YSM
UPC 12 Digit	781810805770
UPC 14 Digit GTIN	00781810805770
Material	Copper
UPC	781810805770

Logistics

Minimum Pack Quantity	200
Carton Quantity	200

Operational

Temperature Rating	90
--------------------	----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2025 Hubbell Incorporated. All rights reserved
BRDY-YSM4C-SPEC-EN | REV 10/2025