

# Catalog

Home &gt; Catalog



Home &gt; 3049-B-632-B



## Swage Standoffs

Model: 3049-B-632-B

## Select Finish

-0 No Plate

## Select Finish

-0 No Plate

Choose a CAD format

### Product Details

These standoffs are made of Brass. They are Round shaped with diameter as 1/4". The thread for this part is 6-32 and length is 3/8".

#### SWAGE TOOLING

±.003	S	P
.075	A	1/32
.105	B	1/16
.135	C	3/32
.165	D	1/8
.230	E	3/16
.290	F	1/4

#### PDF Catalog

[RAF\\_catalog\\_0097.pdf](#)

Thread	6-32
O.D.	1/4"
Shape	Round
Length (L)	3/8"
Material	Brass
RoHS	Yes
Shank Length	0.105"
Board Thickness	1/16"
Shank Diameter	0.188"
Thread Clearance	0.150"
Finish	-0 No Plate



#### Technical Information

[Electronic Hardware Components](#)

[Engineering Data](#)

[Capabilities Brochure](#)

[Services](#)

[Distributors](#)

#### Company

[RAF Quality Management](#)

[Industry Links](#)

[What's New](#)

[News](#)


[About](#)

[Contact](#)

[Careers](#)

#### Contact Us

#### Find Us



95 Silvermine Rd.  
Seymour CT 06483

Downloaded from [Arrow.com](#)