Part Number : 731160020
Product Description : MCRF Right-Angle Plug to Pigtail on 1.32mm Cable, 76.20mm Length, H25, 50 Ohms
Series Number : 73116
Status : Obsolete
Product Category : RF Cable Assemblies



Obsolete

Documents and Resources

Drawings

731160020_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	RF Cable Assemblies
Series	73116
Description	MCRF Right-Angle Plug to Pigtail on 1.32mm Cable, 76.20mm Length, H25, 50 Ohms
Application	RF
Assembly Configuration	Single Ended Connector
Connector to Connector	MCRF-to-Pigtail
Product Name	MCRF
Type	RF Cable Assembly
UPC	884982808362

Electrical

Frequency	6 GHz
Impedance	50Ω

Physical

Cable Length	76.20mm
Gender	Plug/Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	0.310/g
Packaging Type	Bag
Single Ended	Yes
Wire/Cable Type	1.32mm Coaxial

Mates With / Use With

Obsolete

Downloaded from Arrow.com.

Mates with Part(s)

Description	Part Number
MCRF Cable Assemblies	73412

This document was generated on Apr 27, 2026

Obsolete

Downloaded from Arrow.com.