




Part Number : [150310633](#)
Product Description : 0.30mm Pitch Premo-Flex FFC
Jumper with Notches, Same Side Contacts (Type A),
153.00mm Cable Length, Gold (Au) Plating, 33 Circuits
Series Number : 15031
Status : Active
Product Category : Flat-Flexible Cable (FFC)



Documents and Resources

Drawings

- [150310633 sd.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [150310001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15031
Description	0.30mm Pitch Premo-Flex FFC Jumper with Notches, Same Side Contacts (Type A), 153.00mm Cable Length, Gold (Au) Plating, 33 Circuits
Product Name	Premo-Flex FFC Jumper
UPC	195842786899

Electrical

Current - Maximum per Contact	0.2A
Voltage - Maximum	N/A

Physical

Cable Length	152.00mm
Circuits (Loaded)	33
Contact Layout Type	A (same side)
Design Feature	Miniaturization, Superior Retention
Material - Plating Mating	Gold
Net Weight	0.311/g
Packaging Type	Bag
Pitch - Mating Interface	0.30mm
Temperature Range - Operating	-40° to +105°C

Termination Style	FFC Connector
Wire/Cable Type	Flat Flexible Cable (FFC)
Wire Size (AWG)	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Easy-On Back Flip FPC Connector with Lock Terminal, 0.30mm Pitch, LA75 Series, Right-Angle, Surface Mount, Dual Contact Style, 0.75mm Height, 33 Circuits	<u>5047543300</u>

This document was generated on May 25, 2026