
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	07/02/07	
A1	Add wiring color	13/JAN/2012	



PIN OUT:

Male	Female	Color
PIN1	PIN1	Black
PIN2	PIN2	Brown
PIN3	PIN3	Red
PIN4	PIN4	Orange
PIN5	PIN5	Yellow
PIN6	PIN6	Green
PIN7	PIN7	Blue
PIN8	PIN8	Purple
PIN9	PIN9	Gray
PIN10	PIN10	White
PIN11	PIN11	Pink
PIN12	PIN12	Light Green
PIN13	PIN13	Black/White
PIN14	PIN14	Brown/White
PIN15	PIN15	Red/White
SHIELD	SHIELD	Drain Wire

LENGTH & P/N Table

LENGTH	P/N	Cable Color
2.5FT ±1 inch	CS-DSDMDB15MF-002.5	GREY
5FT ±2 inch	CS-DSDMDB15MF-005	GREY
10FT ±3 inch	CS-DSDMDB15MF-010	GREY
15FT ±3 inch	CS-DSDMDB15MF-015	GREY
25FT ±4 inch	CS-DSDMDB15MF-025	GREY
50FT ±8 inch	CS-DSDMDB15MF-050	GREY

NOTES: UNLESS OTHERWISE SPECIFIED

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
DECIMALS .X ±.X .XX ±.XX .XXX ±.XXX
ANGLES ±X°
THIRD ANGLE PROJECTION

EAR NO.

APPROVALS		DATE
DRAWN	LF	13/JAN/2012
CHECKED	BA	13/JAN/2012
RESP ENG		
MFG ENG		

CAD FILE:

Amphenol Cables on Demand
20 VALLEY ST. ENDICOTT, NY 13760

Deluxe 15PIN D-Sub MF

SIZE	DWG. NO.	REV.
A	CS-DSDMDB15MF-XXX	A1

SCALE SHEET OF

Downloaded from Arrow.com.