









[SECTION A–A]

(S=1.2:1)









NOTE

1. MATERIALS

① - HEADER : LIQUID CRYSTAL POLYMER(LCP), UL94V-0, GLASS FILLED, HALOGEN FREE, COLOR OF NATURAL

② - CONTACT TERMINAL : PHOSPHOR BRONZE

2. FINISHES

- CONTACT TERMINAL :
  PURE-TIN PLATING ON OVERALL.
  THICKNESS 2.0μm~4.0μm
  UNDER PLATING Ni OVERALL.
  THICKNESS 1.25μm~3.75μm

RELEASED
EC NO: KOR2014-0120 2014/04/22
DRWN:SCHONG03 2014/04/22
CH'KD:SHCHU 2014/04/22
APPR:YSKIM02 2014/04/22
DESCRIPTION
A
REV

QUALITY SYMBOLS
▼=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.15	± ---
1 PLACE	± 0.20	± ---
0 PLACE	± ---	± ---
ANGULAR ± 1 °		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE: MM ONLY

DRAWN BY	SCHONG03	DATE 2014/04/22
CHECKED BY	SHCHU	DATE 2014/04/22
APPROVED BY	YSKIM02	DATE 2014/04/22

MATERIAL NO. 1041670210

SIZE A3

ORDER NO. 104167-0210

SCALE 5/1 | DESIGN UNITS METRIC | THIRD ANGLE PROJECTION

TITLE: 3.5MM LED DIRECT TYPE CONN. -2P (B-TYPE) HEADER ASS'Y


molex

DOCUMENT NO. SD-104167-001


SHEET NO. 1 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION


Downloaded from Arrow.com.



[1.0t PCB PATTERN]



MATED CONDITION
[FRONT VIEW]



MATED CONDITION
[BACK VIEW]

ORDER NO.	104167-0210

RELEASED
EC NO: KOR2014-0120 2014/04/22
DRWN:SCHONG03 2014/04/22
CH'KD:SHCHU 2014/04/22
APPR:YSKIM02 2014/04/22
DESCRIPTION
A
REV

QUALITY SYMBOLS
▼=0
Ⓒ▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.15	± ---
1 PLACE	± 0.20	± ---
0 PLACE	± ---	± ---

ANGULAR ± 1 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS


DIMENSION STYLE	MM ONLY
SCALE	5/1
DESIGN UNITS	METRIC
	THIRD ANGLE PROJECTION
DRAWN BY	SCHONG03
DATE	2014/04/22
CHECKED BY	SHCHU
DATE	2014/04/22
APPROVED BY	YSKIM02
DATE	2014/04/22
MATERIAL NO.	1041670210
DOCUMENT NO.	SD-104167-001
SHEET NO.	2 OF 2
SIZE	A3


TITLE: 3.5MM LED DIRECT TYPE CONN. -2P (B-TYPE) HEADER ASS'Y


molex

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

Downloaded from Arrow.com.







NOTES.

① 1. PACKING QUANTITY : 48 PCS / TUBE

2. TOTAL TUBE LENGTH : 560mm±1mm

3. BURRS : 0.20mm MAX

ORDER NO.	104167-0210

RELEASED
EC NO: KOR2014-0120 2014/04/22
DRWN:SCHONG03 2014/04/22
CHKD:SHCHU 2014/04/22
APPR:YSKIM02 2014/04/22
DESCRIPTION
A
REV

QUALITY SYMBOLS
▼=0
Ⓒ▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.15	± ---
1 PLACE	± 0.20	± ---
0 PLACE	± ---	± ---

ANGULAR ± 1 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE	MM ONLY
SCALE	10/1
DESIGN UNITS	METRIC
	THIRD ANGLE PROJECTION
DRAWN BY	SCHONG03
DATE	2014/04/22
CHECKED BY	SHCHU
DATE	2014/04/22
APPROVED BY	YSKIM02
DATE	2014/04/22
MATERIAL NO.	SEE TABLE
TITLE	3.5MM LED DIRECT TYPE CONN. -2P (B-TYPE) TUBE PACKING
DOCUMENT NO.	SD-104167-002
SHEET NO.	1 OF 1
SIZE	A3

molex

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

Downloaded from Arrow.com.