Part Number : 1300621121
Product Description : BradPower C-Size (1 1/8”–M29) Double-Ended Cordset, 4 Poles, Tri-Key, Male (Straight) to Female (Straight), 12 AWG, Black TPE Cable, 1.0m (3.28') Length
Series Number : 130062
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 334T30K26M010A3



Documents and Resources

Drawings

1300621121_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c); 6(a)-I per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130062
Description	BradPower C-Size (1 1/8”–M29) Double-Ended Cordset, 4 Poles, Tri-Key, Male (Straight) to Female (Straight), 12 AWG, Black TPE Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Name	BradPower C-Size
Type	Double Ended
UPC	78172557755

Agency

UL	E258922

Electrical

Current - Maximum per Contact	25.0A
Voltage - Maximum	600V

Physical

Cable Diameter	16.66mm (.656")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Connector End A	BradPower C-Size (1 1/8”–M29)
Connector End B	BradPower C-Size (1 1/8”–M29)
Coupling Style	Threaded

Downloaded from Arrow.com.

Gender	Female-Male
Keyway	Tri-Key
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	12

Downloaded from Arrow.com.