

MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BA-2RV22-D81**ABQ1520****BA-2RV22-D81**

PAGE 1 OF 1

MDRAWING
NUMBER

X

X

ISSUE

9

REPLACES

RELEASE NO. PR-2557

18 JAN 06

RJ

CHECK

REVISIONS

A PR-2557

G M

7 APRIL 72

B CO-

7084-6

G J W

7 MAR 92

C CO-

72397

J J O

30 APR 92

D CO-

75204B

J W B

1 FEB 94

E CO-

77590

S A D

10 JUN 94

F C093346

DLT

26 AUG 98

G CO-

94212-C

DLT

20 SEP 99

H 0018387

TSG


18 JAN 06

FORMTEK

FO-50378-1A

DRAWN

OMW 2 FEB 72



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE - - - - - 6 OZ MAX

RELEASE FORCE - - - - - 1 1/2 OZ MIN

PRETRAVEL - - - - - .250 MAX

DIFFERENTIAL TRAVEL - - - - - .045 MAX

OVERTRAVEL - - - - - .030 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T**-L23-** 20A-125, 250 OR 480 VAC; 10A-125 VAC "L"
1HP-125 VAC; 2HP-250 VAC
1/2A-125 VDC; 1/4A-250 VDC**-L288-**
-L308-
-L315-**CE** **05** **RU** **SA**
20(3)A 250V $\sim$ T85 5E4**SCALE FULL**

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:ONE PLACE (.0) $\pm .030$
TWO PLACE (.00) $\pm .015$
THREE PLACE (.000) $\pm .005$
ANGLES $\pm$

WEIGHT .060 LB