




P1



SEC:A-A

P1	P2
1 BLACK	1
2 RED	2
3 GREEN	3
4 YELLOW	4



Note:

- Material: Housing-polycarbonate, clear
- Terminal-0.36[.014] thick phosphor bronze. Thick gold in localized gold plate.
- Area, Gold Flash over the remainder.
- Over 2.54mm[.000100] thick nickel underplate.

Part Number	Drawing Number	Wire Length "L"	Jacket Color	Cut Length
AT-S-26-4/4/S-5-OE	A	1,525±20(5ft)	Silver	1,525-1,535mm
AT-S-26-4/4/S-7-OE	B	2,135±30(7ft)	Silver	2,135-2,145mm
AT-S-26-4/4/S-10-OE	C	3,050±60(10ft)	Silver	3,050-3,060mm
AT-S-26-4/4/S-12-OE	D	3,660±60(12ft)	Silver	3,660-3,670mm
AT-S-26-4/4/S-14-OE	E	4,270±60(14ft)	Silver	4,270-4,280mm
AT-S-26-4/4/S-25-OE	F	7,625±100(25ft)	Silver	7,625-7,635mm
AT-S-26-4/4/S-50-OE	G	15,250±150(50ft)	Silver	15,250-15,260mm

Unit: mm

RoHS
Compliant

Scale	Free					Date	Name
TOLERANCE					Drawn	28.06.13	Wilson
X.	±X				Approved	28.06.13	Groll
X.X	±X						
X.XX	±X						
DIM	TOL						
X.°	±X°						
X.X°	±X°						
Angle	TOL						
		Id.	Modification	Date	Name		

ASSMANN
components
1940 W. Drake Drive, Suite 101 • Tempe, AZ 85283
Toll Free: 1-877-277-6266 • Email: info@assmann.us

Title	Modular cable - Straight/Open
	4P4C 50µ", 26AWG, Silver, 5-50 feet
ASSMANN WSW-No.	AT-S-26-4/4/S-xx-OE
Drawing-No.	
Replace	rev00
Sheet	1/1