Part Number : 1120361000
Product Description : IP20 Unmanaged Ethernet Switch, 5 Ports, 10/100Mb Data Speed
Series Number : 112036
Status : Active
Product Category : Industrial Ethernet Switches
Engineering Part Number : DRL-250MB



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Industrial Ethernet Switches
Series	112036
Description	IP20 Unmanaged Ethernet Switch, 5 Ports, 10/100Mb Data Speed
Approvals	CE, FCC, UL
Comments	10/100 Base TX (Mbaud)
IP Rating	IP20
Product Name	IP20 Unmanaged Ethernet Switch
Protocol	EtherNet (IEEE 802.3)
Switch Functionality	Unmanaged
UPC	78172561271

Electrical

Data Speed	Fast Ethernet (10/100Mbps)
EMC	CE, EN 610006-2-4, FCC Part 15, ICES-003
Supply Voltage	24V DC

Physical

Ethernet Connector	RJ45
Housing Depth	73.80mm
Housing Length	109.20mm
Housing Width	23.40mm
MAC Address	2048
Mechanical Shock	IEC 60068-2-27
Mounting Style	DIN Rail, Wall
Packaging Type	Carton
Ports	5
Power Input	24V DC
Temperature Range - Operating	-40° to +70°C
Uplink Connection	N/A
Vibration	IEC 60068-2-6

Downloaded from Arrow.com.

Downloaded from Arrow.com.