



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/30/10	
A		REVISED SHAPE	6/18/12	



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: White

Electrical:

Voltage rating: 125 VAC/DC max

Current rating: 1 Amp max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 16, 18, 20, 22, 24, 26, 28, 30
A = .049 [1.25] X No. of Spaces
B = .049 [1.25] X No. of Spaces + .057 [1.45]
C = .049 [1.25] X No. of Spaces - .049 [1.25]
DIM. C 2P, 3P (NONE)

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

0.049 [1.25] PITCH CRIMP HOUSING

SINGLE ROW, 2 THRU 30 POSITIONS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				TITLE			
.X	± .10	ØX	± .10	Holes			
.XX	± .020	ØXX	± .015	Holes			
.XXX	± .015	ØXXX	± .010	Holes			
APPROVALS				DATE			
DRAWN	AY		11/30/10				
CHECKED	AH		11/30/10				
APPROVED							
REF: S00123T				SCALE: NTS			
SHEET 1 OF 1							