
Part Number : 2058272043
Product Description : ConnTAK50 Tang Receptacle, Single Row, 4 Circuits, Key C, Blue
Series Number : 205827
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

2058272043_sd.pdf

PK-31301-538-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2046310000-AS-000.pdf

2046310000-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	205827
Description	ConnTAK50 Tang Receptacle, Single Row, 4 Circuits, Key C, Blue
Application	Automotive, Wire-to-Board
Component Type	Receptacle
Product Name	ConnTAK50
UPC	193264109111

Physical

Circuits (maximum)	4
Color - Resin	Blue
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	0.589/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.80mm
Pitch - Termination Interface	1.80mm
Polarization	C

Downloaded from Arrow.com.

Polarized to Mating Part	Yes
Sealed	Unsealed
Stackable	No
Temperature Range - Operating	-40° to +100°C USCAR Class T2, -40° to +105°C LV-214
Terminal Size	0.5

Mates With / Use With

Mates with Part(s)

Description	Part Number
ConnTAK50 Right-Angle, Single Row, Surface Mount Headers	208033
ConnTAK50 Vertical, Single Row, Surface Mount Headers	208035

Use with Part(s)

Description	Part Number
TAK50 Receptacle Terminal, Unsealed, L-Grip, D-Wind, Left Reel Payoff	2000963101
TAK50 Receptacle Terminal, Unsealed, L-Grip, B-Wind, Right Reel Payoff	2000963161
TAK50 Receptacle Terminal, Unsealed, S-Grip, D-Wind, Left Reel Payoff	2000963201
TAK50 Receptacle Terminal, Unsealed, S-Grip, B-Wind, Right Reel Payoff	2000963261

Downloaded from Arrow.com.