

Data Sheet | Item Number: 248-453
Mini-WSB marking card; as card; MARKED; U1, ... U10 (10x); not stretchable; Horizontal marking; snap-on type; white
<https://www.wago.com/248-453>



Color: white

Similar to illustration

Technical data	
Marking method	Thermal transfer
Marking	U1, ... U10
Marking (number)	10
Marking direction	Horizontal marking
Marking color	black
Marking type	Symbol
Marking layout	Consecutive symbols each strip
Delivery form	Marker card
Delivery form configuration	10 strips with 10 markers per card

Physical data	
Height	152 mm / 5.984 inches
Width	56.8 mm / 2.236 inches
Depth	3.2 mm / 0.126 inches
Marker/strip width	5 mm
Marker width	5 mm

Mechanical data	
Smear resistance	EN 60998-1:2004

Material data	
Color	white
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	6.2 g
Fire load	0.185 MJ



Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	50 (5) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332656528
Customs tariff number	49119900000

Product Classification	
UNSPSC	55121718
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 9.0	EC000761
ETIM 8.0	EC000761
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 248-453

↓

Documentation			
Bid Text			
248-453	19.02.2019	xml 2.68 KB	↓
248-453	16.03.2018	doc 23.50 KB	↓

Installation Notes

Marking



Marking via Mini-WSB Quick Marking System.