Hello, Your privacy is important to us. On May 24, 2018, we published an updated Privacy Statement. Please read these updated terms. We use cookies to create the most secure and effective website possible. By using this site, you consent to the use of cookies. Full details in our Privacy Statement.
Click here to not show this message again

Products



Previous Next







Vuquest 3310g Hands-Free Scanner

Honeywell's Vuquest® 3310g compact area-imaging scanner offers aggressive scanning of all 1D, PDF and 2D barcodes in a lightweight, durable and portable form factor. The 3310g hands-free scanner's sleek and elegant design also blends seamlessly in retail environments. With intelligent multi-interface design, this image scanner supports popular interfaces on a single device and features mobile phone reading technology to scan barcodes on mobile devices.

Feature and Benefits | Accessories | Documents | Software | Links

Vuquest 3310g Hands-Free Scanner Accessories

Power
46-00525 STD Power Supply: NA plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz
46-00526 STD Power Supply: EU plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz
46-00870 STD Power Supply: UK plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz
46-00528 STD Power Supply: AU plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz
46-00529 STD Power Supply: CN plug, 1.0A @ 5.2VDC, 90-255VAC @ 50-60Hz

Cables
52-52557-3-FR Cable: RS232, black, DB9, 5V, 2.9m (9.5') straight
52-52558-N-3-FR Cable: KBW, black, PS2, 5V, 2.9m (9.5') straight
52-52559-N-3-FR Cable: USB, black, Type A, 5V, 2.9m (9.5') straight
52-52561-3-FR Cable: USB, black, Type A, 5V, 2.9m (9.5') straight, External IO
52-52562-3-FR Cable: RS232black, DB9, 5V, 2.9m (9.5') straight, External IO

Stand/Holder
46-01210: Vuquest presentation-tray stand

Related Products



EasyDL®
TotalFreedom Plug-In

EZConfig

Ezconfig - Device Configuration Software

Remote MasterMind

Remote MasterMind Device Management Software

Honeywell Repair Services

Downloaded from Arrow.com.



© 2018 Honeywell International Inc.

Downloaded from Arrow.com.