

Catalog No. TC050X050A-C

Description: 4-WAY MNTG BASE .5X.5IN NAT NYL ADH

UPC No 786210492957

Home > Wire & Cable Management > Deltec > Cable tie mounts

Four-Way Adhesive Mini Mounting Base, Natural Nylon 6.6 for Temperatures up to 65 Degrees Celsius (149 F), Length of 12.7mm (0.50 Inches), Width of 12.7mm (0.50 Inches), Height of 4.52mm (0.178 Inches), Slot Width of 5.59 (0.22 Inches), Self-Adhesive Mounting Method, 100 Pack

Representative Image

Descriptors

Category	Cable tie mounts
Special Features	Eliminates errors in premounting the base with respect to its orientation to wire bundle direction.

Specifications

Number Of Entries	4
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Adhesive
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap
------------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	12.7 mm
Length	0.5 inch
Width	12.5 mm
Width	0.5 inch
Height	4.52 mm
Height	0.18 inch
Type of fastening	Self-adhesive
Material	Plastic
Material quality	Polyamide (PA)

by ABB

ETIM	EC000449 Mounting base and -element for cable ties
Colour	Natural colour