



PRODUCT NUMBER	PITCH
TSxx11xB00J0G	3.50 mm



Material

- Item ① Clamp: Brass (CuZn), Nickel plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Female contact: PhBz, Tin plated
- Item ④ Top body: Thermoplastic (UL94V-0)
- Item ⑤ Bottom body: Thermoplastic (UL94V-0)

Electrical cULus/VDE

- Voltage rating: 300VAC/300VAC
- Current rating: 8A/10A
- Wire range: 1.5mm²
- Solid wire (AWG): 16-28
- Stranded wire (AWG): 16-28
- Torque: 1.7Lb-In./0.2Nm
- Screw: M2
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval: 

DIMENSION

Dim A	NX3.5
Dim B	(N-1)X3.5
Dim C	(N-1)X3.5

N=Number of poles

Poles	Tolerance
2P-8P	±0.10
9P-16P	±0.20
17P-24P	±0.30

PART NO.: TS xx 11 x B 00J0 G

Solid block	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
02	2 poles	Black (RAL9005)	
03	3 poles	Red (RAL3001/D)	
...	...	Orange (RAL2011/P)	
...	...	Yellow (RAL1018/A)	
24	24 poles	Green (RAL6018/T)	
...	...	Blue (RAL5015/A)	
...	...	Grey (RAL7035/D)	
...	...	White (RAL1102)	
...	...	Green (RAL6018/U)	

mat'l. code				surface	tolerance	projection	product family			
ltr ecn no dr date				ASME Y14.5 ✓	ASME Y14.5		TERMINAL BLOCK			
				tolerances unless otherwise specified		MM	title			
				angles	X.±0.5		TERMINAL BLOCK			
				size	X.X±0.3		PLUGGABLE PLUG, HOOK ON BACK SIDE, WITHOUT FLANGE			
				X'±1"	X.XX±0.1	scale	dwg no sheet 1 of 1 size			
				dr	EVIN ZHONG 041814		TSxx11xB00J0G			
				enrg	EVIN ZHONG 041814		A4			
				chr	HANKE FENG 041814		type CUSTOMER Drawing			
				appd	SHI JUN 041814					
sheet index	revision	A	1							