



Part Number : [1300950291](#)
Product Description : Multi-Weave Wire Mesh Pulling Grip, Flexible Eye, Mesh Length 1.321m (52.00"), Approximate Break Strength 11158.37kg (24600 lbs)
Series Number : 130095
Status : Obsolete
Product Category : Cable Grips
Engineering Number : 36643



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Cable Grips
Series	130095
Description	Multi-Weave Wire Mesh Pulling Grip, Flexible Eye, Mesh Length 1.321m (52.00"), Approximate Break Strength 11158.37kg (24600 lbs)
Comments	Color Identifier Gold, Eye Cable Thickness 1/2"
Product Name	Multi-Weave
Type	Pulling Grip
UPC	78678836643

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	11158.37kg (24600 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	25.40-31.50mm (1.000-1.240")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	1.321m (52.00")
Net Weight	1406.140/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A