



**Part Number :** [399400411](#)

**Product Description :** 5.08mm Pitch Beau EuroMate Pluggable Terminal Block, Dual Level, 90° Wire Entry, with Retention Screws, 11 Circuits

**Series Number :** 39940

**Status :** Active

**Product Category :** Terminal Blocks and Barrier Strip

**Engineering Part Number :** 946811



---

## Documents and Resources

### Drawings

[399400411\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[PS-39940-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39940
Description	5.08mm Pitch Beau EuroMate Pluggable Terminal Block, Dual Level, 90° Wire Entry, with Retention Screws, 11 Circuits
Application	Wire-to-Board
Comments	Gold plating available
Component Type	Plug
Product Name	EuroMate Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	800756372945

### Agency

UL	E48521
----	--------

### Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

### Physical

Circuits (Loaded)	11
Circuits (maximum)	11
Color - Resin	Black
Entry Angle	Horizontal
Flammability	94V-0
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.000/g
Number of Rows	2
Orientation	N/A
Panel Mount	No
PCB Retention	N/A
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Polarized to Mating Part	Yes
Shrouded	Tri-Barrier
Stackable	No
Temperature Range - Operating	130°C
Termination Interface Style	Screw or Lug
Wire Size (AWG)	12, 14, 16, 18, 20, 22
Wire Size mm <sup>2</sup>	0.50-2.50

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
5.08mm Pitch Eurostyle Vertical PCB Header, with Threaded Retention Inserts, 11 Circuits	<a href="#"><u>395350011</u></a>
5.08mm Pitch Eurostyle Right-Angle PCB Header, with Threaded Retention Inserts, 11 Circuits	<a href="#"><u>395360011</u></a>

---

This document was generated on Apr 12, 2026