

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)[Home](#) / [Products](#) / [Ceres](#) / [Middle Size](#)

Product Line

[Single Pair Ethernet](#) >[ZConnect](#) >[Ceres](#) >[Accessory](#)[Large Size](#)[Macro Size](#)[Middle Size](#)[Mini Size](#)[Others \(GBD\)](#)[Others \(MAB\)](#)[Others \(PLD\)](#)[Standard Size](#)[X-Lok](#) >[M Series](#) >[FLOS & FLOS+](#) >[Power](#) >[RBL](#) >[HS-Lok](#) >[NMEA 8888](#) >

ABOUT AMPHENOL LTW

[Heavy Duty Shielded](#) >[RJ](#) >[USB](#) >[SSL](#) >[HDMI](#) >[DVI](#) >[Fiber Optic](#) >[RF](#) >[Cable Joiner](#) >[Cable Gland](#) >[Pressure Relief Vent](#) >[LED Light Guide](#) >[D-Sub](#) >

ACB-04PMFS-LC7001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: UL1977

You must login first for view the price

Quantity

- 1 +

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

Ceres, Middle Size,...
1CB-04BFMM-LL6A01
-20°C ~ +80°C

Ceres, Middle Size,...
1CB-04BFMM-LL6A02
-20°C ~ +80°C

Ceres, Middle Size,...
1CB-04BFMM-LL6A03
-20°C ~ +80°C

Ceres, Middle Size,...
1CB-04BFMM-LL6A04
-20°C ~ +80°C

Specifications	Download / CAD
Nominal Current 10A	Connector Type Receptacle
Shielded Plastic, Non-shielded	No. of Contacts 04
Connector Gender Male	Backshell Circular
Mating Style 2 Points Lock	IP Rating IPX7
Assembly Style Solder	
More Options	

People Also Bought

