

6

5

4

3




2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/8/22	



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0, Glow Wire Compliant

Insulator color: White

Contacts: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 600 V

Current rating: 2~4P: 13A, 6~10P: 11A

Dielectric withstanding voltage: 5000 VAC for 1 minute

Temperature Rating:

-55°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 10

A = .250 [6.35] x No. of Positions + .050 [1.27]

B = .250 [6.35] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	ØX ±.10
.XX ±.020	ØXX ±.015
.XXX ±.015	ØXXX ±.010

DRAWN	LH	8/8/22
CHECKED	YC	8/8/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH**ADAM
TECH**909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710TITLE
WIRE TO BOARD, FEMALE, 6.35mm PITCH
WITH POLARIZING, SINGLE ROW TYPE

SIZE X	PART NO. DME-F-XX-S-P-S-V0-GW	REV. -
REF: S00123T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1