

Portable Charger - 2x USB-A, 10,000mAh Power Bank, Lithium-Ion, LED Flashlight, Black

MODEL NUMBER: **UPB-10K0-2U**



Charge your mobile device anywhere, anytime without plugging into an AC power outlet. Ideal for cellphones, smartphones, tablets, e-readers, MP3 players and Bluetooth speakers, headsets and headphones.

Description

No more frantic searching for an AC power outlet when your cellphone, tablet, or other mobile device's battery power is getting low. The UPB-10K0-2U Portable 10,000mAh Dual-Port Mobile Power Bank is the perfect power solution when you're on the road, or stuck somewhere without convenient electricity. It fits comfortably in your purse, backpack or laptop bag to keep your e-reader, MP3 player, handheld game console or Bluetooth device operating when you need it.

Just connect your device to the UPB-10K0-2U's USB-A port using the included USB Micro-B cable or another cable suitable for your device. Press the on/off button to illuminate the LEDs that indicate the Mobile Power Bank's battery capacity at a glance. Press the button twice to use the unit as an LED flashlight.

The portable UPB-10K0-2U's dual USB ports provide up to 5V, 1A and 5V, 2A of power, so you can charge two devices at once. Its 10,000mAh capacity charges devices at maximum power up to 3.3 hours. It protects against short circuits, overvoltage, over-current, overcharges and overdischarges. Charge the Mobile Power Bank by connecting its USB Micro-B port to a USB charger or a computer's USB-A port using the included cable. Press the on/off button, and the four LEDs will blink or light solid in various combinations to indicate the battery level.

Features

Travel-Sized for Convenient Charging of Dual Devices Anywhere

- Fits comfortably in your purse, backpack, or laptop bag
- Ideal for charging cellphones, tablets, e-readers, MP3 players, handheld game consoles and Bluetooth headsets, headphones and speakers
- USB Micro-B charging cable included

Superior Charge Capability Without an AC Power Outlet

- Connect USB-A port to device for charging at maximum output up to 3.3 hr.
- Dual USB ports provide up to 5V, 1A and 5V, 2A of power at 10,000mAh capacity
- Protects against short circuits, overvoltage, over-current, overcharges and overdischarges

Built-In Lithium-Ion Battery

Highlights

- Fits comfortably in your purse, backpack or laptop bag
- Dual USB ports provide up to 5V, 1A and 5V, 2A of power
- LEDs indicate remaining battery capacity
- Charges devices at maximum output up to 3.3 hr.
- Includes USB Micro-B charging cable

Package Includes

- UPB-10K0-2U Portable 10,000mAh Dual-Port Mobile Power Bank USB Battery Charger
- USB Micro-B cable, 3 ft.
- Owner's Manual



Powering Business Worldwide



- Connect the power bank's USB Micro-B port to a USB charger or a computer's USB-A port to charge internal battery
- Built-in LEDs indicate how much battery capacity is left
- Unit also functions as a convenient LED flashlight

Specifications

OVERVIEW	
UPC Code	037332189387
Product Type	Portable Charger
Charging Form Factor	Portable
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	5V DC
Input Plug Type	USB MICRO-B (FEMALE)
Input Plug Type Details	USB-A to USB Micro B cable provided
OUTPUT	
Overload Protection	Yes
CONNECTIONS	
Side A - Connector 1	(2) USB A (FEMALE)
Side B - Connector 1	USB 3.0 MICRO-B (FEMALE)
CHARGING	
Number of Charging Ports	2
Total Charging Amps	2A
Total Charging Watts	10
Charging Method	USB
Charging Method Detail	10,000 mAh
Charging Port Type	(2) USB A (FEMALE)
Charging Ports Details	USB-A: 5V/1A or 5V/2A
Charging Ports / Amps	(1) 1A; (1) 2A
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	1.80 x 4.70 x 9.30
Shipping Dimensions (hwd / cm)	4.57 x 11.94 x 23.62



Powering Business Worldwide



Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	2.3 x 7.8 x 12.0
Unit Weight (lbs.)	0.6
Unit Weight (kg)	0.27
ENVIRONMENTAL	
Operating Temperature Range	32F to 113F (0C to 45C)
Storage Temperature Range	5F to 140F (-15C to 60C)
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.