
# PXP6043/A3 Datasheet

## Product Name // Plastic Body Front Panel Mount Leaded USB Connector Sealed 3.0 A Socket Front of Panel To 10 Way Crimp Connector

View Product Page






## // Product Description:

- Plastic Body Front Panel Mount Leaded Connector
- Water and dustproof to IP68 & IP69K when mated with compatible connector
- 30 degree push twist locking, tamperproof lock prevents accidental un-mating
- Sealed Standard USB 3.0 socket to lead cable terminated in 10 way crimp connector
- PXP6083 Sealing Cap available separately to maintain IP rating of unmated connectors
- Mate with Plastic Body USB A Cables

## // General Information:

| | |
|---|---|
| **Product Display Title:** | Plastic Body Front Panel Mount Leaded USB Connector Sealed A Socket Front of Panel To 10 Way Crimp Connector |
| **Product Family:** | Circular Data Connectors |
| **Product Series:** | 6000 Series - USB Buccaneer |
| **Body Material:** | Polycarbonate/Polybutylene Terephthalate (PC/PBT) |
| **Body Material Type:** | Plastic Body |
| **Contact Type:** | Socket Contact |
| **Coupling Type:** | Push-Twist |
| **Current Max:** | 1A |
| **Data Cable Type:** | Sealed A Socket to 10 Way Crimp |
| **Diameter Over Coupling Ring Mm:** | 32mm |
| **Flamability Rating:** | UL94V-0 |
| **Ip Rating:** | IP66, IP68, IP69K |
| **Max Operating Temperature:** | +70°C |
| **Min Operating Temperature:** | 0°C |
| **Number Of Contacts:** | 8 Contacts |
| **Voltage Max:** | 30V |

### // Product PDF Links

6000 Series HDMI Product Data

### // Product 3D CAD Model Links

PXP6043/A33D CAD Model

Have a question or project enquiry you'd like to talk to us about?

Click Here To Contact Us

Downloaded from Arrow.com.