



Technical Data

12.04.2021

Heat shrinkable tubing - PTFE
TFE4 - 4:1 shrink ratio

TFE4-1/8

Article Number 339-00329



Material: Polytetrafluoroethylene (PTFE)

Colour: Transparent (CL)

Supplied Ø D min.: 3.17 mm

Recov. Ø d max.: 0.94 mm

Wall (WT): 0.25 mm

Shrink Ratio: 4:1

Longitudinal Change After Shrinkage: -20 % max.

Min. Shrink Temperature - °C: +330 °C

Test Method

Flammability: non-burning

Operating Temperature - °C: -65 °C to +260 °C

Dielectric Strength: 40 kV/mm

DIN 53481

Tensile Strength: 39 MPa



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved