
HellermannTyton

Technical data sheet

Article number:
170-01008 Twist-In 38



Product Group	Self-closing polyester sleeving
Product Family	Helagaine Twist-In
Material	Polyester (PET)
Colour	Black (BK)

Application Method	For optimum cable protection including flexibility, we recommend that a filling level of 75% is not exceeded.
Bundle Ø max.	38 mm
Bundle Ø min.	32 mm
Melting Point	+255 °C
Operating Temperature	-50 °C to +125 °C
Package Content	15 m
Package Content packed in	reel
UL-File Number	E197993

HF ✓ RoHS ✓

created on 4. September 2026, 9:40 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.