

# AI 0,75-10 WH - Ferrule

2100114

<https://www.phoenixcontact.com/ae/products/2100114>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ferrule, Length contact range: 10 mm, sleeve length: 16 mm, color: white



## Your advantages

- The insulation reliability of close connections is increased and the splicing of wires is prevented

## Commercial data

Item number	2100114
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BH3
Product key	BH3411
GTIN	4067923214408
Weight per piece (including packing)	0.1 g
Weight per piece (excluding packing)	0.1 g
Customs tariff number	85369010
Country of origin	DE

# AI 0,75-10 WH - Ferrule

2100114

<https://www.phoenixcontact.com/ae/products/2100114>

## Technical data

### Product properties


Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	UL certified
	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of DIN 46228-1 and UL 486F in terms of size
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

### Connection data

#### Conductor connection

Conductor cross-section flexible max.	0.75 mm <sup>2</sup>
Conductor cross-section AWG max.	18
Stripping length	13 mm

### Dimensions

Dimensional drawing	
Sleeve length	16 mm
Length contact range	10 mm
Maximum stripping length	13 mm
Ferrule diameter	1.3 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.25 mm
Inner dimensions of the insulating collar	2.8 mm

### Material specifications

Color	white (RAL 9010)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

### Mechanical properties

#### Technical data

# AI 0,75-10 WH - Ferrule

2100114

<https://www.phoenixcontact.com/ae/products/2100114>



Sleeve length	16 mm
---------------	-------

## Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

# AI 0,75-10 WH - Ferrule

2100114

<https://www.phoenixcontact.com/ae/products/2100114>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/ae/products/2100114>



**cULus Listed**

Approval ID: E488001

# AI 0,75-10 WH - Ferrule



2100114

<https://www.phoenixcontact.com/ae/products/2100114>

## Classifications

### ECLASS

ECLASS-13.0	27400201
ECLASS-15.0	27400201

### ETIM

ETIM 9.0	EC000005
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# AI 0,75-10 WH - Ferrule



2100114

<https://www.phoenixcontact.com/ae/products/2100114>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Middle East FZ LLC  
1201N-1206N, Dubai Science Park Towers – North  
P.O. Box 345002, Dubai, United Arab Emirates  
(+971) 4 437-0324  
[info-me@phoenixcontact.com](mailto:info-me@phoenixcontact.com)