



Specifications:  
 Current rating:1.0A AC,DC  
 Voltage rating:250V AC, DC  
 Contact tesistance:20m ohm Max  
 Insulation resistance:1,000M ohm Min  
 Withstanding voltage:500V AC/minute  
 Operating Temperature:-40°C ~ +105°C

Material:  
 Insulator:PBT UL94V-0  
 Color:Black  
 Coctact:Copper Alloy  
 Plating:Selective Gold Plated

CIRCUITS	DIM.A	DIM.B	DIM.C
10	15.20	8.00	9.00
14	19.20	12.00	13.00
16	21.20	14.00	15.00
20	25.20	18.00	19.00
26	31.20	24.00	25.00
40	45.20	38.00	39.00
50	55.20	48.00	49.00

RoHS Compliant

				DRAWN:	GENERAL TOLERANCE: .X=±0.20 .XX=±0.15	<b>CnC Tech</b> Industrial Cable and Connector Technology	DESCRIPTION: 2.0mm IDC Socket Without Strain Relief	SIZE <b>A4</b>
				CHECKED:				
					SCALE: 1:1			
A	01-DEC-2020			APPROVAL:	SHEET: 1 / 1	PART NO:	3130-XX-0102-00	
REV	DATE	FILE	BY		PROJECTION:			