Part Number : 395265003
Product Description : 5.00mm Pitch Eurostyle Right-Angle PCB Header, with Threaded Retention Inserts, Green Housing, 3 Circuits
Series Number : 39526
Status : Active
Product Category : Terminal Blocks and Barrier Strip



Documents and Resources

Drawings

395265003_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

PS-39500-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39526
Description	5.00mm Pitch Eurostyle Right-Angle PCB Header, with Threaded Retention Inserts, Green Housing, 3 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Eurostyle Pluggable
Type	PCB Terminal Blocks and Connectors
UPC	822350513111

Agency

UL	E48521

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Physical

Downloaded from Arrow.com.

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Green
Entry Angle	N/A
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Horizontal
Panel Mount	No
PCB Thickness - Recommended	3.20mm
PC Tail Length	3.90mm
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Polarized to Mating Part	Yes
Shrouded	Closed Ends
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
5.00mm Pitch Eurostyle Horizontal Plugs	39524
5.00mm Pitch Eurostyle Plugs	39527
Mates With	Most 5.00mm Pitch Industry Standard Plugs

Downloaded from Arrow.com.