

**Part Number :** [1300030048](#)

**Product Description :** Quick-Change Receptacle, 4 Pole, 1/2" - 14 NPT, Male (Straight) to 14 AWG Leads, 0.30m (11.81") Length

**Series Number :** 130003

**Status :** Active

**Product Category :** Circular Industrial Connectors

**Engineering Part Number :** 32632

---

## Documents and Resources


### Drawings

[1300030048 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## CE - Declaration of Conformity

## UKCA - Declaration of Conformity

---

## Part Details

### General

Status	Active
Category	Circular Industrial Connectors
Series	130003
Description	Quick-Change Receptacle, 4 Pole, 1/2" - 14 NPT, Male (Straight) to 14 AWG Leads, 0.30m (11.81") Length
IP Rating	IP67
Product Name	Quick-Change
Type	Single Ended (pigtail)
UPC	78678832632

### Agency

CSA	LR6837
UL	E46237

### Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	600V AC/DC

### Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	0.305m
Material - Component	Nylon
Mounting Thread Size	1/2" - 14 NPT

Net Weight	199.000/g
Orientation	Straight
Panel Mount	Front
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 1015
Wire Size (AWG)	14

---

This document was generated on May 09, 2026